

TECHSPEC® 25.4mm Sq., 2X, Protected Aluminum Off-Axis Ellipsoidal Mirror



Protected Aluminum Off-Axis Ellipsoidal Mirror

Stock **#12-495** [CONTACT US](#)



1



£242.25

ADD TO CART

Qty 1-5

£242.25

Qty 6+

£218.03

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Magnification:
2X

Substrate:
Aluminum 6061-T6

Surface Quality:
60-40

Surface Roughness (Angstroms): <100 RMS
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating Type: Metal
Dimensions (mm): 25.40 x 25.40
Off-Set Angle (°): 72.89
Type: Off-Axis Ellipsoidal Mirror
Wavelength Range (nm): 400 - 2000
Y Offset (mm): 38.10
Image Distance (mm): 50.80
Object Distance (mm): 25.40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View