

TECHSPEC® 25.4mm Protected Gold $\lambda/10$ Knife-Edge Pickoff Mirror



25.4mm Enhanced Protected Gold $\lambda/10$ D-Shaped Pickoff Mirror, #36-136

Stock **#36-136** 3-4 DAYS

⊖ 1 ⊕ **£85.00**

ADD TO CART

Qty 1-5
£85.00

Qty 6+
£76.50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40

Surface Flatness (P-V):
 $\lambda/10$

Substrate: ⓘ
[Fused Silica](#) (Coming 7980)

Back Surface: Fine Grind
Surface Quality: 20-10
Dimensional Tolerance (mm): +0.0/-0.20
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Edges: Ground
Parallelism (arcmin): 2
Thickness (mm): 6.35
Thickness Tolerance (mm): ±0.20
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: ☐ 0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant