

TECHSPEC® 25.4mm x -75mm FL, VIS 0° Imaging Grade PCV Cylinder Lens



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock **#34-664** 3-4 DAYS

⊖ 1 ⊕ **£94.35**

ADD TO CART

Qty 1-5
£94.35

Qty 6+
£75.22

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.0/-0.025

Effective Focal Length EFL (mm):
-75.00

Substrate: ⊞
[N-BK7](#)

f/#: 3
Numerical Aperture NA: 0.17
Coating: VS 0° (425-675nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -77.31
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 5.57
Radius R₁ (mm): 38.76
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant