


TECHSPEC®

25mm 632nm, Laser Line Non-Polarizing Beamsplitter



Laser Line Non-Polarizing Cube Beamsplitters



Stock **#35-963** 3-4 DAYS

⊖ 1 ⊕

£234.60

ADD TO CART

Qty 1-5
£234.60
Qty 6+
£187.85
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcmin):
±2

Bevel:
Protective as needed

Clear Aperture (%): 90
Coating Specification: <0.25% Reflection on Entrance and Exit Faces
Construction: Cube
Design Wavelength DWL (nm): 632
Dimensions (mm): 25.0 x 25.0 x 25.0 ±0.1
Reflection/Transmission Tolerance (%): ±5
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Transmission (%): <45% ±5% @ DWL
Type: Non-Polarizing Beamsplitter
[Ts-Tp]: <3% @ DWL

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View