

TECHSPEC[®] 25mm Dia 50R/50T, VIS Plate Beamsplitter



Visible and NIR Plate Beamsplitters

Stock #35-942 3-4 DAYS

-

1

+

£100.30

ADD TO CART

Qty 1-5

£100.30

Qty 6+

£80.75

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
45

Clear Aperture (%):
>85

Coating Specification:
Surface 1: 50/50 ±5% @ 550nm, ±10% @ 400 -

700nm, Surface 2: AR R _{avg} ≤1%, R _{abs} ≤2% @400 - 700nm
Construction: Plate
Diameter (mm): 25.00
Edges: Cut with 0.25mm maximum edge chip
Note: Beamsplitter-coated side is marked with a black dot
Parallelism (arcmin): ≤3
Reflection/Transmission Ratio (R/T): 50/50
Substrate: ☐ N-BK7
Surface Flatness (P-V): 2λ per inch
Surface Quality: 60-40
Thickness (mm): 1.00 ±0.1
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
