

25mm Dia., 800nm, Corning Polarcor™ Glass Polarizer



Corning Polarcor™ Glass Polarizers

Stock **#13-613** [CONTACT US](#)

- 1 + **£1,670.25**

ADD TO CART

Qty 1+
£1,670.25

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0 ±5

Coating:
BBAR (740-860nm)

Design Wavelength DWL (nm):
800

Diameter (mm):
25.00

Extinction Ratio: >10,000:1
Substrate: Borosilicate Glass Containing Elongated Silver Crystals
Minimum Transmission (%): >91.3
Surface Quality: 40-20
Thickness (mm): 0.50 ±0.05
Dimensional Tolerance (mm): ±0.1
Coating Specification: R_{avg} <0.4% @ 740 - 860nm
Wavelength Range (nm): 740 - 860
Insertion Loss (dB): <0.39
Index of Refraction n_d: 1.5161
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 6.5
Knoop Hardness (kg/mm²): 480
Young's Modulus (GPa): 58.605
Poisson's Ratio: 0.21
Abbe Number (v_d): 57.6
Density (g/cm³): 2.412

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View