

**TECHSPEC® 25mm Dia x 20mm FL, NIR I Coated, Molded Aspheric Condenser Lens**



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#15-732** 3-4 DAYS

[Other Coating Options](#)

- 1 + **£49.30**

ADD TO CART

|          |
|----------|
| Qty 1-10 |
| £49.30   |

|         |
|---------|
| Qty 11+ |
| £43.35  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):  
20.00 @ 587.6nm

Numerical Aperture NA:

|                                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------|
| 0.625                                                                                                           |
| <b>Back Focal Length BFL (mm):</b><br>11.93                                                                     |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Liba2000+</a>                                         |
| <b>Focal Length Tolerance (%):</b><br>±5                                                                        |
| <b>Coating:</b><br>NIR I (600-1050nm)                                                                           |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.5% @ 600 - 1050nm                                          |
| <b>Centering (arcmin):</b><br>≤25                                                                               |
| <b>Surface Quality:</b><br>Molded Side: 5/3 x 0.4; E 0.2<br>Polished Side: 5/3 x 0.25; E 0.2                    |
| <b>Clear Aperture CA (mm):</b><br>22.28                                                                         |
| <b>Edge Thickness ET (mm):</b><br>3.21                                                                          |
| <b>Center Thickness CT (mm):</b><br>12.27 ±0.30                                                                 |
| <b>f/#:</b><br>0.8                                                                                              |
| <b>Bevel:</b><br>Protective bevel as needed                                                                     |
| <b>Diameter of Asphere (mm):</b><br>25.00                                                                       |
| <b>Radius R<sub>2</sub> (mm):</b><br>∞                                                                          |
| <b>Shape of Back Surface:</b><br>Plano                                                                          |
| <b>Type:</b><br>Condenser Lens                                                                                  |
| <b>Wavelength Range (nm):</b><br>600 - 1050                                                                     |
| <b>Conjugate Distance:</b><br>Infinite                                                                          |
| <b>Note:</b><br><a href="#">Click here</a> for more information on the ISO 10110 surface quality specification. |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |