

TECHSPEC® 25mm Dia., 5mm Thick, YAG-BBAR Coated, λ/10 Fused Silica Window



Stock #13-356 3-4 DAYS

- 1 + **£136.00**

ADD TO CART

Qty 1-5
£136.00
Qty 6+
£108.80
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
67.8

Bevel:
Protective as needed

Clear Aperture (%):
80

Clear Aperture CA (mm): 20.00
Diameter (mm): 25.00 +0.00/-0.20
Thickness (mm): 5.00 ±0.10
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R_{abs} <0.25% @ 532nm R_{abs} <0.25% @ 1064nm R_{avg} <1.0% @ 500 - 1100nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm³): 2.20
Edges: Fine Ground
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcsec): <5
Poisson's Ratio: 0.16
Substrate: Fused Silica (Corning 7980)
Surface Quality: 20-10
Transmitted Wavefront, P-V: λ/10
Type: Protective Window
Wavelength Range (nm): 500 - 1100
Young's Modulus (GPa): 73
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant