

TECHSPEC® 25mm Dia. x 25mm FL, Uncoated, 266nm DWL, CaF₂ Aspheric Lens



TECHSPEC® Calcium Fluoride (CaF₂) Aspheric Lenses

Stock **#13-463** 3-4 DAYS



1



£428.40

ADD TO CART

Qty 1-5

£428.40

Qty 6+

£385.56

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
25.00 @ 266nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 18.78
Substrate: ☐ Calcium Fluoride (CaF ₂) Vacuum UV Grade
Aspheric Design Wavelength (nm): 266
Asphere Figure Error, RMS @ 632.8nm: λ/6
Coating: Uncoated
Centering (arcmin): <1
Surface Quality: 60-40
Clear Aperture CA (mm): 22.50
Edge Thickness ET (mm): 3.75
Center Thickness CT (mm): 11.00 ±0.10
f#: 1.00
Edges: Diamond Turned
Type: Aspheric Lens
Wavelength Range (nm): 200 - 7000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View