

25mm Dia. KRS-5, IR Holographic Wire Grid Polarizer



Stock #62-774 3-4 DAYS

- 1 + **£1,530.00**

ADD TO CART

Qty 1-5
£1,530.00

Qty 6+
£1,224.00

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
18.0

Diameter (mm):
25.00

Extinction Ratio: 150:1 @ 3µm, 300:1 @ 15µm
Substrate: ☐ Thallium Bromoiodide (KRS-5)
Operating Temperature (°C): -20 to 75
Polarization: Notches on polarizer ring are aligned with wires of wire grid
Thickness (mm): 2.00
Transmission (%): >60
Type: Linear Polarizer
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Construction: Wire Grid
Groove Parallelism to Edge (°): N/A
Mount Thickness (mm): 5.0
Note: Notches on polarizer ring are aligned with wires of wire grid (max. reflection)
Ring Thickness (mm): ±0.1
Wavelength Range (nm): 2500 - 30000
Surface Flatness (P-V): N/A
Damage Threshold, By Design: ☐ 50 W/cm ²
Mount: Black Anodized Aluminum
Groove Density (grooves/mm): 2700.00
Mount Thickness Tolerance (mm): +0.2/-0.1

Regulatory Compliance

RoHS: Compliant
Reach 219: Compliant
Certificate of Conformance: View