


TECHSPEC[®] 25mm Dia., Uncoated, $\lambda/10$ Stemmed Mirror



Stock #14-577 CLEARANCE 3-4 DAYS

-

1

+

£101.15

ADD TO CART

Qty 1-5

£101.15

Qty 6+

£80.75

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Diameter (mm):

25.00 +0.00/-0.10

Substrate: Fused Silica (Corning 7980)
Surface Quality: 10-5
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Clear Aperture (%): 90.00
Back Surface: Commercial Polish
Surface Flatness (P-V): λ/10
Coating Type: Uncoated
Edges: Ground, protective bevel as needed
Stem Diameter (mm): 12.50 +0.00/-0.10
Compatible Kinematic Mount: #58-853
Stem Length (mm): 6.50 ±0.20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View