

TECHSPEC®

25mm VIS-EXT, 50R/50T, Non-Polarizing Cube Beamsplitter



Stock #11-289 3-4 DAYS



1



£240.55

ADD TO CART

Qty 1-5

£240.55

Qty 6+

£188.70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating: VIS-EXT (400-640nm)
Coating Specification: R _{avg} <0.5% @ 400 - 640nm
Construction: Cube
Dimensions (mm): 25.0 x 25.0 x 25.0 ±0.1
Reflection/Transmission Ratio (R/T): 50/50
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 400 - 640
 Ts-Tp : <6%
Absolute Transmission (%): 45 ±10

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View