

TECHSPEC® 25mm C VIS-NIR Series Fixed Focal Length Lens



25mm Focal Length, #67-715

Stock **#67-715** ☒ In Stock



1



£365.00

ADD TO CART

Qty 1+

£365.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
30.50

Horizontal Field of View, 1/2" Sensor:
25.4mm - 14.5°

Horizontal Field of View, 2/3" Sensor:
35mm - 19.8°

Filter Thread:

M25.5 x0.50 (Female)
Maximum Diameter (mm): 31
Outer Diameter (mm): 31.0
Weight (g): 48
Horizontal Field of View, 1/3" Sensor: 19mm - 10.9°
Maximum Rear Protrusion (mm): 1.39
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0706
Horizontal Field of View @ Max Sensor Format: 36.5mm - 19.8°
Number of Elements (Groups): 7 (6)
Horizontal Field of View, 1/1.8" Sensor: 29.9mm - 16.2°
Horizontal Field of View, 1/2.5" Sensor: 24.0mm - 13.1°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Primary Magnification PMAG: 0.243
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Coating: 425 - 1000nm BBAR
Coating Specification: 425 - 1000nm BBAR
Entrance Pupil Position (mm): 17.14
Horizontal Field of View, 1/4" Sensor: 14.9mm - 8.2°
Object Space Principal Plane (mm): 18.74
Image Space Principal Plane (mm): -12.43
Field of View at Max Sensor Format: Horizontal: 36.6mm - 19.8° Vertical: 27.4mm - 14.9° Diagonal: 45.9mm - 24.6°
Maximum Distortion (%): 0.22
Exit Pupil Position (mm): -14.14
Lens Wavelength Range: VIS-NIR
Imaging Lens Type: Compact Lens Coated for Visible to Near Infared
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View

