

TECHSPEC® 25mm Dia. x 50mm EFL, UV-VIS Coated, Near UV Achromatic Lens



Stock #65-976 ☒ In Stock

-

1

+

£133.88

ADD TO CART

Qty 1-5

£133.88

Qty 6+

£107.10

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
50.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 44.74
Focal Length Specification Wavelength (nm) : 405.00
Clear Aperture CA (mm) : 24.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 10.50 ±0.20
Center Thickness CT 1 (mm) : 8.00 ±0.10
Center Thickness CT 2 (mm) : 2.50 ±0.10
Radius R₁ (mm) : 30.03
Radius R₂ (mm) : -24.15
Radius R₃ (mm) : -63.90
Edge Thickness ET (mm) : 6.54
Substrate : ☐ N-FK5 / F2H1
Surface Quality : 40-20
f/# : 2
Numerical Aperture NA : 0.25
Coating : UV-VIS (345-700nm)
Coating Specification : R _{avg} ≤1.5% @ 345 - 700nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 345 - 700

Regulatory Compliance

RoHS 2015 : Exempt
Certificate of Conformance : View
Reach 235 : Compliant