

TECHSPEC®

241 - 271nm, 12.7mm Dia., Ultrafast Mirror



Stock #11-734

3-4 DAYS

-

1

+

£158.95

ADD TO CART

Qty 1-5

£158.95

Qty 6+

£139.40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:

10-5

Type:

Laser Mirror

Typical Applications:

Ti:Sapphire 3rd Harmonic

Clear Aperture (%) : >80
Coating Specification: R _s >98.5% @ 235 - 280nm R _p >97.5% @241 - 271nm
GDD Specification: 0 ±10fs ² @ 241 - 271nm
Wavelength Range (nm): 241 - 271
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Ultrafast (241-271nm)
Design Wavelength DWL (nm): 266
Diameter (mm): 12.70 +0.00/-0.10
Thickness (mm): 6.35 ±0.10
Angle of Incidence (°): 45
Substrate: ☐ Fused Silica (Coming 7980)
Parallelism (arcsec): <10
Damage Threshold, By Design: ☐ 0.26 J/cm ² @ 258nm, 177fs FWHM, P-polarization, 1 pulse (typical) 0.2 J/cm ² @ 258nm, 177fs FWHM, 10kHz, P-polarization, 1000 pulses (typical) 0.3 J/cm ² @ 258 nm, 1 ps FWHM, 100 Hz, P-polarization, 1000 pulses

Regulatory Compliance

RoHS 2015: Compliant
Reach 205: Compliant
Certificate of Conformance: View