

TECHSPEC® 25mm f/5.6, HPr Series Fixed Focal Length Lens



25mm HPr Series Lens

Stock #36-522 3-4 DAYS

⊖ 1 ⊕ **£616.25**

ADD TO CART

Qty 1+

£616.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Fixed

Length (mm):
48.23

Filter Thread:
M34 x 0.50 (Female)

Maximum Diameter (mm):
29.2

Weight (g):

78

Maximum Rear Protrusion (mm):

4.48

Horizontal Field of View, 1" Sensor:

86.1mm - 28.4°

Maximum Image Circle (mm):

17.60

Numerical Aperture NA, Object Side:

0.0124

Horizontal Field of View @ Max Sensor Format:

95.9mm - 31.3°

Horizontal Field of View, 1.1" Sensor:

95.9mm - 31.3°

Number of Elements (Groups):

7 (6)

Front Thread:

M27.5 x 0.5 (Female)

Type:

Fixed Focal Length Lens

Focal Length FL (mm):

25.00

Primary Magnification PMAG:

0.155

Maximum Sensor Format:

1.1"

Working Distance (mm):

150 - ∞

Mount:

C-Mount

Aperture (f/#):

f/5.6

Coating:M4 MgF₂**Coating Specification:**M4 MgF₂**Entrance Pupil Position (mm):**

28.11

Object Space Principal Plane (mm):

34.43

Image Space Principal Plane (mm):

-13.27

Field of View at Max Sensor Format:

Horizontal: 92.6mm - 31.1°

Vertical: 68.8mm - 23.6°

Diagonal: 117.3mm - 38.3°

Maximum Distortion (%):

0.1

Exit Pupil Position (mm):

-21.69

Optimized Working Distance (mm):

150 - ∞

Lens Wavelength Range:

VIS

Storage Temperature (°C):

-20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS:[Compliant](#)**Certificate of Conformance:**[View](#)