

Richardson Gratings™ 300 Grooves, 12.5 x 12.5mm, 1200nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock #37-119 3-4 DAYS

-

1

+

£111.35

ADD TO CART

Qty 1+

£111.35

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
300

Wavelength Range (nm):

750 - 2000
Blaze Wavelength (nm): 1200 ±25
Blaze Angle (°): 10.4
Peak Efficiency, Typical (%): 92
Dimensions (mm): 12.5 x 12.5 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Ruled Grating
Length (mm): 12.50
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 12.50
Reflected Wavefront, RMS: λ/4
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: S and P
Master Reference: 0938
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View