

TECHSPEC® 30mm Dia., 0.58 NA, Uncoated, NIR Aspheric Lens



TECHSPEC® Near-Infrared (NIR) Aspheric Lenses

Stock #13-504 3-4 DAYS

[Other Coating Options](#)



1



£267.75

ADD TO CART

Qty 1-5

£267.75

Qty 6+

£214.20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 +0.00/-0.10

Effective Focal Length EFL (mm):
26.00 @ 780nm

Numerical Aperture NA:

0.58
Back Focal Length BFL (mm): 20.57
Substrate: □ S-LAH64
Aspheric Design Wavelength (nm): 780
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 27
Edge Thickness ET (mm): 3.82
Center Thickness CT (mm): 9.65 ±0.10
f#: 0.87
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 375 - 2100
Conjugate Distance: Infinite
Power (diopters): 38.46

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View