

TECHSPEC® 30mm Dia x 24mm FL, NIR I Coated, Molded Aspheric Condenser Lens



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#15-733** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

£51.85

ADD TO CART

Qty 1-10

£51.85

Qty 11+

£45.90

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.3

Effective Focal Length EFL (mm):
24.00 @ 587.6nm

Numerical Aperture NA:

0.625
Back Focal Length BFL (mm): 14.73
Substrate: ☐ Liba2000+
Focal Length Tolerance (%): ±5
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/5 x 0.63; E 0.4 Polished Side: 5/5 x 0.25; E 0.4
Clear Aperture CA (mm): 26.78
Edge Thickness ET (mm): 3.21
Center Thickness CT (mm): 14.10 ±0.30
f/#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 30.00
Radius R₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant