

TECHSPEC®

31.75mm Dia., 1mm Thick, VIS-NIR AR Coated Sapphire Window



Stock **#39-249**

3-4 DAYS

-

1

+

£148.75

ADD TO CART

Qty 1-24

£148.75

Qty 25+

£119.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
72.24

Axis Orientation:
Random

Bevel:
Protective as needed

Birefringence (n_o - n_e):
0.008 for Visible Light Orthogonal to Optical Axis

Clear Aperture (%):
≥90

Clear Aperture CA (mm):
28.58

Diameter (mm):
31.75 ±0.25

Thickness (mm):
1.00 ±0.05

Coating:
VIS-NIR (400-1000nm)

Coating Specification:
R_{avg} ≤0.25% @880nm
R_{avg} ≤1.25% @400 - 870nm
R_{avg} ≤1.25% @890 - 1000nm

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
8.8

Density (g/cm³):
3.97

Edges:
Fine Ground

Index of Refraction n_d :
1.77

Knoop Hardness (kg/mm²):
1900

Parallelism (arcmin):
≤3.5

Poisson's Ratio:
0.27

Substrate:
Sapphire (Al₂O₃)

Surface Flatness (P-V):
2λ (typical)

Surface Quality:
80-50

Type:
Protective Window

Wavelength Range (nm):
400 - 1000

Young's Modulus (GPa):
435

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)