

TECHSPEC®

# 31.75mm Sq., 2.5X, Protected Gold Off-Axis Ellipsoidal Mirror



Protected Gold Off-Axis Ellipsoidal Mirror

Stock #12-498 3-4 DAYS



1



£284.75

ADD TO CART

Qty 1-5

£284.75

Qty 6+

£256.27

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Magnification:  
2.5X

Substrate:  
Aluminum 6061-T6

Surface Quality:  
60-40

|                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------|
| <b>Surface Roughness (Angstroms):</b><br><100 RMS                                                                |
| <b>Coating:</b><br>Protected Gold (700-10000nm)                                                                  |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >96% @ 700 - 2000nm<br>R <sub>avg</sub> >96% @ 2000 - 10,000nm |
| <b>Coating Type:</b><br>Metal                                                                                    |
| <b>Dimensions (mm):</b><br>31.75 x31.75                                                                          |
| <b>Off-Set Angle (°):</b><br>65.44                                                                               |
| <b>Type:</b><br>Off-Axis Ellipsoidal Mirror                                                                      |
| <b>Wavelength Range (nm):</b><br>700 - 10000                                                                     |
| <b>Y Offset (mm):</b><br>49.38                                                                                   |
| <b>Image Distance (mm):</b><br>83.82                                                                             |
| <b>Object Distance (mm):</b><br>33.02                                                                            |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |