

TECHSPEC[®] 30mm Dia., 0.50 Numerical Aperture Uncoated, Aspheric Lens



Stock #66-312 ☐ In Stock

[Other Coating Options](#)

-

1

+

£263.50

ADD TO CART

Qty 1-5

£263.50

Qty 6+

£210.80

Volume Pricing

[Request Quote](#)

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.1

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Numerical Aperture NA:

0.50
Back Focal Length BFL (mm): 22.99
Substrate: L-BAL35
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 27
Edge Thickness ET (mm): 4.81
Center Thickness CT (mm): 11.70 ±0.1
f#: 1.00
Bevel: Protective bevel as needed
Radius R ₂ (mm): 300
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 330 - 2400
Conjugate Distance: Infinite
Power (diopters): 33.33

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View