

3.0mm FL, IR-Cut Filter at 650nm, f/2, Micro Video Lens



Stock **#66-886** ☒ In Stock

[Similar Products](#)



1



£50.15

ADD TO CART

Qty 1-49

£50.15

Qty 50+

£39.95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
15.30

Filter Thread:
M12 x0.50

Maximum Diameter (mm):
14.0

Maximum Image Circle (mm): 6.00
Horizontal Field of View @ Max Sensor Format: 97.8
Resolution, On-Axis: 97 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 62 lp/mm @ 20% Contrast
Resolution, Full Field: 35 lp/mm @ 20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 3.00
Maximum Sensor Format: 1/3"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2
Distortion (%): -52.10 @ Full Field
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View