

355nm Flat Top Beam Shaper | πShaper 12_12_355_HP

See More by [AdlOptica](#)



Stock **#15-497** [CONTACT US](#)

- 1 + **£8,146.40**

ADD TO CART

Qty 1-4
£8,146.40

Qty 5+
£7,332.10

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):

355

Diameter (mm):

42.00

Entrance Beam Diameter, 1/e² (mm):

12.0 - 12.1

Model Number: πShaper 12_12_355_HP
Length (mm): 358.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <530
Wavelength Range (nm): 330 - 380
Style: Flat Top
Damage Threshold, By Design: ☐ 3 J/cm² @ 5ns (typical)
Output Diameter, FWHM (mm): 11.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant