

# 340nm CWL, 10nm FWHM, 25mm Mounted Diameter



Stock #65-674 CLEARANCE 3-4 DAYS

- 1 + **£114.71**

ADD TO CART

|         |
|---------|
| Qty 1+  |
| £114.71 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

|                       |
|-----------------------|
| Get Product Downloads |
|-----------------------|



|                                              |
|----------------------------------------------|
| <b>Diameter (mm):</b><br>25.00 +0.0/-0.2     |
| <b>Angle of Incidence (°):</b><br>0          |
| <b>Optical Density OD (Average):</b><br>≥3.0 |
| <b>Clear Aperture CA (mm):</b><br>21.0       |

|                                                        |
|--------------------------------------------------------|
| <b>Center Wavelength CWL (nm):</b><br>340.00 ±2        |
| <b>Center Wavelength CWL Tolerance (nm):</b><br>±2     |
| <b>Full Width-Half Max FWHM (nm):</b><br>10.00 ±2      |
| <b>Full Width-Half Max FWHM Tolerance (nm):</b><br>±2  |
| <b>Minimum Transmission (%):</b><br>≥25                |
| <b>Operating Temperature (°C):</b><br>-50 to +75       |
| <b>Coating:</b><br>Traditional Coated                  |
| <b>Surface Quality:</b><br>80-50                       |
| <b>Thickness Tolerance (mm):</b><br>±0.1               |
| <b>Type:</b><br>Bandpass Filter                        |
| <b>Typical Applications:</b><br>FURAExcitation         |
| <b>Blocking Wavelength Range (nm):</b><br>200 - 1200   |
| <b>Construction:</b><br>Mounted in Black Anodized Ring |
| <b>Mount Thickness (mm):</b><br>7.5 ±0.1               |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |