

## TECHSPEC® 375nm 25mm Dia., High Performance Longpass Filter



High Performance OD 4.0 Longpass Filters

Stock #34-302 [CONTACT US](#)

1 **£221.00**

**ADD TO CART**

Qty 1-5

£221.00

Qty 6+

£189.55

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
25.00 +0/-0.2

**Angle of Incidence (°):**  
0

**Optical Density OD (Average):**

≥4.0

**Cut-On Wavelength (nm):**  
375.00

**Substrate:**   
[Fused Silica](#) (Coming 7980)

**Coating:**  
Hard Coated

**Rejection Wavelength (nm):**  
200 - 365

**Surface Quality:**  
60-40

**Thickness (mm):**  
1.50

**Thickness Tolerance (mm):**  
±0.1

**Transmission (%):**  
>91

**Transmission Wavelength (nm):**  
383 - 1600

**Type:**  
Longpass Filter

**Clear Aperture (%):**  
>80

**Transmitted Wavefront, RMS:**  
≤λ/4 @ 633nm (prior to coating)

**Cut-On Tolerance (%):**  
±1

**Slope Factor (%):**  
1.00

**Environmental Durability:**  
Humidity per MIL-STD-810H, Section 507.6  
Temperature per MIL-STD-810H, Section 501.7 and 502.7

**Physical Durability:**  
Adhesion per MIL-PRF-13830B, Section C.4.5.12  
Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11  
Cleaning per MIL-C-48497A Section 4.5.4.2

**Coating Specification:**  
Surface 1: Hard Dielectric Sputtered  
Surface 2: AR Coated

**Wavelength Range (nm):**  
200 - 1600

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**REACH 241:**  
[Compliant](#)

---