


TECHSPEC® 38.1 x 25.4mm 1064nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock #39-662 3-4 DAYS

⊖ 1 ⊕ **£151.30**

ADD TO CART

Qty 1-5

£151.30

Qty 6+

£133.45

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):
85

Back Surface:
Commercial Polish

Reflection at DWL (%):
99.8

Coating Specification:
 $R_{\text{abs}} > 99.8\% @ 1064\text{nm}$

Surface Flatness (P-V):
λ/10

Coating Type:
Dielectric

Coating:
Laser Mirror (1064nm)

Design Wavelength DWL (nm):
1064

Dimensions (mm):
38.1 x 25.4 +0.00/-0.10

Thickness (mm):
6.35 ±0.20

Angle of Incidence (°):
0-45

Substrate:
[Fused Silica](#) (Coming 7980)

Damage Threshold, Reference:
15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 209:
[Compliant](#)

Certificate of Conformance:
[View](#)