

## TECHSPEC® 38.1mm Diameter Enhanced Aluminum Coated, λ/10 Mirror



Stock #39-217 3-4 DAYS

⊖ 1 ⊕ **£124.95**

**ADD TO CART**

Qty 1-5

£124.95

Qty 6+

£99.88

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
38.10 +0.00/-0.20

**Surface Flatness (P-V):**  
λ/10

**Substrate:**   
[Fused Silica](#) (Coming 7980)

**Back Surface:**  
Commercial Polish

**Surface Quality:**  
20-10

**Dimensional Tolerance (mm):**  
+0.0/-0.10

**Coating Specification:**  
R<sub>avg</sub> >95% @ 450 - 650nm

**Coating:**  
Enhanced Aluminum (450-650nm)

**Coating Type:**  
Metal

**Bevel:**  
Protective bevel as needed

**Clear Aperture (%):**  
90

**Edges:**  
Ground

**Parallelism (arcsec):**  
<180

**Thickness (mm):**  
6.35 ±0.20

**Type:**  
Flat Mirror

**Wavelength Range (µm):**  
0.45 - 0.65

**Wavelength Range (nm):**  
450 - 650

**Damage Threshold, Reference:**   
0.2 J/cm<sup>2</sup> @ 532nm, 10ns

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**REACH 241:**  
[Compliant](#)