

# 4 OD, 25mm Dia., VIS 0° Coated, Absorptive ND Filter

See More by [Hoya](#)



Anti-Reflection (AR) Coated HOYAAbsorptive Neutral Density (ND) Filters

Stock #13-111 3-4 DAYS

-

1

+

**£62.05**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| £62.05                        |
| Qty 11+                       |
| £55.25                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00

Optical Density OD (Average):  
4 ±0.2 @ 400-700nm (Uncoated Filter)

Nominal Optical Density @ Center of Coating:

|                                                                       |
|-----------------------------------------------------------------------|
| 3.60 @ 550nm                                                          |
| <b>Glass/Filter Number:</b><br><a href="#">Hoya ND-006</a>            |
| <b>Substrate:</b> <input type="checkbox"/><br>ND Filter Glass         |
| <b>Coating:</b><br>VS 0° (425-675nm)                                  |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.531                 |
| <b>Surface Quality:</b><br>80-50                                      |
| <b>Transformation Temperature (°C):</b><br>542                        |
| <b>Thickness (mm):</b><br>2.85                                        |
| <b>Thickness Tolerance (mm):</b><br>±0.5                              |
| <b>Transmission (%):</b><br>0.01 (average) @ 400 - 700nm              |
| <b>Type:</b><br>Neutral Density Filter                                |
| <b>Blocking Wavelength Range (nm):</b><br>400 - 700                   |
| <b>Dimensional Tolerance (mm):</b><br>±0.1                            |
| <b>Parallelism (mm):</b><br><0.02                                     |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm |
| <b>Wavelength Range (nm):</b><br>425 - 675                            |
| <b>Stock No. of Uncoated Filter:</b><br><a href="#">#36-273</a>       |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |