

TECHSPEC[®] 38.1mm Dia., 6.35mm Thick, Fused Silica Uncoated Laser Window Substrate



TECHSPEC[®] Uncoated Laser Window Substrates

Stock #38-912 3-4 DAYS

⊖

1

⊕

£167.88

ADD TO CART

Qty 1-5

£167.88

Qty 6+

£151.30

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
34.29

Coating:
Uncoated

Diameter (mm):
38.10 +0.00/-0.10

Substrate: Fused Silica (Corning 7980)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Window Substrate
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 67.8
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/10
Fused Silica Grade: 7980 0F
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View