

TECHSPEC[®] 4.0 OD 12.5mm Dia., NIR ND Filter



Near-IR (NIR) Neutral Density (ND) Filters

Stock #36-265 3-4 DAYS

-

1

+

£69.70

ADD TO CART

Qty 1-5

£69.70

Qty 6+

£55.76

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Optical Density OD (Average):
4.00

Substrate:
[Fused Silica](#) (Corning 7980)

Coating: Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.10
Transmission (%): 0.01
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 700 - 1100
Clear Aperture (%): 80
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant