


400nm, 25mm Dia., OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock #15-222 3-4 DAYS

⊖ 1 ⊕

£88.40

ADD TO CART

Qty 1-9

£88.40

Qty 10+

£79.56

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-On Wavelength (nm): 400.00 ±8
Substrate: 
Coating: Hard Coated
Rejection Wavelength (nm): 200 - 375
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 425 - 1600
Type: Longpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 200 - 1600

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View