


400nm, 6 x 6mm, OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock **#15-198** 3-4 DAYS

⊖ 1 ⊕ **£38.25**

ADD TO CART

Qty 1-9
£38.25
Qty 10+
£34.42
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads	
Dimensions (mm): 6.00 x 6.00 +0.00/-0.20	
Angle of Incidence (°): 0	
Optical Density OD (Average): ≥2.0	

Cut-On Wavelength (nm): 400.00 ±8
Substrate: 
Length (mm): 6.00
Coating: Hard Coated
Rejection Wavelength (nm): 200 - 375
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 425 - 1600
Type: Longpass Filter
Width (mm): 6.00
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 200 - 1600

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View