


LightPath 356300 | 4mm Dia., 0.66 NA, BBAR (350-600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-677** ☐ In Stock

-

1

+

£80.75

ADD TO CART

Qty 1-10
£80.75
Qty 11+
£70.97
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
4.00 ±0.015

Effective Focal Length EFL (mm):
2.54 @405nm

Numerical Aperture NA: 0.66
Substrate:  L-LAL12
Aspheric Design Wavelength (nm): 405
Coating: BBAR (350-600nm)
Coating Specification: R _{abs} <1.0% @ 350 - 600nm
Surface Quality: 40-20
Clear Aperture CA (mm): 3.30
Edge Thickness ET (mm): 0.77
Center Thickness CT (mm): 1.82 ±0.05
f/#: 0.76
Bevel: Protective bevel as needed
Lightpath Lens Code: 356300
Type: Aspheric Lens
Wavelength Range (nm): 350 - 600
Working Distance (mm): 1.55
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant