

TECHSPEC[®] 40mm Dia x 40mm FL, Uncoated, High Precision Aspheric Lens



TECHSPEC[®] High Precision Aspheric Lenses

Stock #12-445 3-4 DAYS

[Other Coating Options](#)



1



£735.25

ADD TO CART

Qty 1-10

£735.25

Qty 11+

£577.15

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 +0.00/-0.025

Effective Focal Length EFL (mm):
40.00 @ 587.6nm

Numerical Aperture NA:

0.50
Back Focal Length BFL (mm): 31.21
Substrate: ☐ N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: λ/40
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 36.00
Edge Thickness ET (mm): 6.83
Center Thickness CT (mm): 14.70
f#: 1
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 380 - 2500
Conjugate Distance: Infinite
Note: 3D Surface Profile included with uncoated lenses
Power (diopters): 25.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View