

4.0mm FL, High Resolution, f/1.8, Micro Video Lens



Stock #11-324 3-4 DAYS

-

1

+

£62.90

ADD TO CART

Qty 1-49
£62.90
Qty 50+
£48.45
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
23.80

Maximum Diameter (mm):
20.0

Maximum Image Circle (mm):
9.00

Horizontal Field of View @ Max Sensor Format:

118.2
Resolution, On-Axis: 100 lp/mm @ 69.3% Contrast
Resolution, 0.7 Field: 100 lp/mm @ 56.0% Contrast
Resolution, Full Field: 100 lp/mm @ 48.4% Contrast
Note: High Resolution
TV Distortion (%): -38.7
Type: M12 Imaging Lens
Focal Length FL (mm): 4.00
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/1.8
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View