

4.3mm FL, High Resolution, f/2, Micro Video Lens



Stock **#88-590** ☒ In Stock

-

1

+

£62.90

ADD TO CART

Qty 1-49
£62.90
Qty 50+
£48.45
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
21.50

Maximum Diameter (mm):
22.0

Maximum Image Circle (mm):
6.60

Horizontal Field of View @ Max Sensor Format:

Resolution, On-Axis:
100 lp/mm @ 72.0% Contrast

Resolution, 0.7 Field:
100 lp/mm @ 56.0% Contrast

Resolution, Full Field:
100 lp/mm @ 46.0% Contrast

Note:
High Resolution

TV Distortion (%):
-0.4

Type:
M12 Imaging Lens

Focal Length FL (mm):
4.30

Maximum Sensor Format:
1/2.7"

Working Distance (mm):
400 - ∞

Mount:
M12 x 0.5 (S-Mount)

Aperture (f/#):
f/2

IR Cut Filter:
No

Lens Wavelength Range:
VIS

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)