


TECHSPEC® 40mm Diameter, BBAR (1650-3000nm) Coated, Calcium Fluoride Window



TECHSPEC Calcium Fluoride (CaF₂) Windows

Stock #15-970 3-4 DAYS

⊖ 1 ⊕ **£231.63**

ADD TO CART

Qty 1-10

£231.63

Qty 11+

£208.46

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
94.99

Axis Orientation:
Random

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):
36.00

Diameter (mm):
40.00 +0.0/-0.1

Thickness (mm):
3.00 ±0.1

Coating:
BBAR (1650-3000nm)

Coating Specification:
R_{avg} <1% @ 1650 - 3000nm
R_{abs} <2% @ 1650 - 3000nm

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
18.85

Density (g/cm³):
3.18

Edges:
Fine Ground

Index of Refraction n_d:
1.434

Knoop Hardness (kg/mm²):
158.3

Parallelism (arcmin):
<1

Poisson's Ratio:
0.26

Substrate:
Calcium Fluoride (CaF₂) Vacuum UV Grade

Surface Flatness (P-V):
λ/2

Surface Quality:
40-20

Type:
Protective Window

Wavelength Range (nm):
1650 - 3000

Young's Modulus (GPa):
75.8

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)