


450nm, 25mm Dia., OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock #15-223 3-4 DAYS

-

1

+

£88.40

ADD TO CART

Qty 1-9
£88.40
Qty 10+
£79.56
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-On Wavelength (nm): 450.00 ±9
Substrate: 
Coating: Hard Coated
Rejection Wavelength (nm): 200 - 425
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 475 - 1600
Type: Longpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 200 - 1600

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View