

TECHSPEC® 45mm Dia., 0.70 NA, Uncoated, NIR Aspheric Lens



TECHSPEC® Near-Infrared (NIR) Aspheric Lenses

Stock **#13-505** 3-4 DAYS

[Other Coating Options](#)



1



£374.00

ADD TO CART

Qty 1-5

£374.00

Qty 6+

£299.20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
45.00 +0.00/-0.10

Effective Focal Length EFL (mm):
32.00 @ 780nm

Numerical Aperture NA:

0.70
Back Focal Length BFL (mm): 24.18
Substrate: □ S-LAH64
Aspheric Design Wavelength (nm): 780
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 40.5
Edge Thickness ET (mm): 3.02
Center Thickness CT (mm): 13.90 ±0.10
f#: 0.71
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 375 - 2100
Conjugate Distance: Infinite
Power (diopters): 31.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View