

TECHSPEC® 473nm, 25mm Diameter, Raman Edge Filter



Stock #86-239 [CONTACT US](#)

-

1

+

£603.50

ADD TO CART

Qty 1-9
£603.50
Qty 10+
£501.50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Optical Density OD (Average):
≥6.0

Cut-On Wavelength (nm): 477.70
Design Wavelength DWL (nm): 473
Substrate:  Fused Silica (Corning 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 383 - 473
Surface Quality: 60-40
Thickness Tolerance (mm): +0.1/-0.1
Transmission (%): >93
Type: Longpass Filter
Transition Width (nm): <4.7
Clear Aperture (%): >80
Durability: Environmental: MIL-STD-810F Physical: MIL-C-48497A
Transmitted Wavefront, RMS: <λ/4 @ 633nm
Mount Thickness (mm): 3.5
Note: Bandwidth (nm): >550
Coating Specification: T _{avg} ≥93% @ 479.1 - 1066.9nm
Wavelength Range (nm): 383 - 1067
Laser Blocking Wavelength (nm): 473.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View