

TECHSPEC® 488nm, 25mm Diameter, Raman Edge Filter



Stock #86-240 ☐ In Stock

1 **£603.50**

ADD TO CART

Qty 1-9
£603.50
Qty 10+
£501.50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Optical Density OD (Average):
≥6.0

Cut-On Wavelength (nm): 492.90
Design Wavelength DWL (nm): 488
Substrate:  Fused Silica (Corning 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 394 - 488
Surface Quality: 60-40
Thickness Tolerance (mm): +0.1/-0.1
Transmission (%): >93
Type: Longpass Filter
Transition Width (nm): <4.9
Clear Aperture (%): >80
Durability: Environmental: ML-STD-810F Physical: ML-C-48497A
Transmitted Wavefront, RMS: <λ/4 @ 633nm
Mount Thickness (mm): 3.5
Note: Bandwidth (nm): >600
Coating Specification: T _{avg} ≥93% @ 494.3 - 1100.8nm
Wavelength Range (nm): 394 - 1101
Laser Blocking Wavelength (nm): 488.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View