


TECHSPEC® 4mm Dia. Laser Mirror Substrate



TECHSPEC® Laser Mirror Substrates

Stock #12-681 3-4 DAYS

- 1 + **£85.85**

ADD TO CART

Qty 1-10

£85.85

Qty 11+

£75.65

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror Substrate

Parallelism (arcmin):
<3

Clear Aperture (%):	90
Back Surface:	Commercial Polish
Surface Flatness (P-V):	λ/10
Coating:	Uncoated
Diameter (mm):	4.00 +0.00/-0.10
Thickness (mm):	3.00 ±0.20
Substrate:	Fused Silica (Corning 7980)

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View