

TECHSPEC® 4mm Dia. 1064nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock #12-629 [CONTACT US](#)

1 **£96.90**

ADD TO CART

Qty 1-5

£96.90

Qty 6+

£85.85

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):

<3

Clear Aperture (%):

90

Back Surface:

Commercial Polish

Reflection at DWL (%):

99.8

Coating Specification:R_{abs} >99.8% @ 1064nm**Wavelength Range (nm):**

1046 - 1074

Surface Flatness (P-V):

λ/10

Coating Type:

Dielectric

Coating:

Laser Mirror (1064nm)

Design Wavelength DWL (nm):

1064

Diameter (mm):

4.00 +0.00/-0.10

Thickness (mm):

3.00 ±0.20

Angle of Incidence (°):

0-45

Substrate: [Fused Silica](#) (Corning 7980)**Damage Threshold, Reference:** 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS:[Compliant](#)**Certificate of Conformance:**[View](#)