

50.0mm FL, IR-Cut Filter at 650nm, f/2.5, Micro Video Lens



Stock **#66-897** 3-4 DAYS

- 1 + **£62.90**

ADD TO CART

Qty 1-49
£62.90

Qty 50+
£48.45

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
52.80

Filter Thread:
M12 x0.50

Maximum Diameter (mm):
27.0

Maximum Image Circle (mm):

8.00
Horizontal Field of View @ Max Sensor Format: 6.8
Resolution, On-Axis: 160 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 100 lp/mm @ 20% Contrast
Resolution, Full Field: 80 lp/mm @ 20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 50.00
Maximum Sensor Format: 1/2"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2.5
Distortion (%): -1.20 @ Full Field
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View