

TECHSPEC® 50.0mm Diameter x 75.0mm FL, 633nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#69-457** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

£59.92

ADD TO CART

Qty 1-9
£59.92

Qty 10+
£53.98

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Effective Focal Length EFL (mm): 75.00 @ 587.6nm
Back Focal Length BFL (mm): 67.70
Coating: Laser V-Coat (633nm)
Coating Specification: R _{abs} <0.25% @ 633nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 11.00 ±0.10
Edge Thickness ET (mm): 1.86
Radius R₁ (mm): 38.76
Clear Aperture CA (mm): 49
f/#: 1.5
Numerical Aperture NA: 0.33
Design Wavelength DWL (nm): 633
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 5 J/cm ² @ 633nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant