

TECHSPEC® 50.8 x 50.8mm EFL 90° Protected Silver 100Å Off-Axis Parabolic Mirror



Stock #36-594

CONTACT US

Other Coating Options



1



£416.50

ADD TO CART

Qty 1-5

£416.50

Qty 6+

£374.85

Volume Pricing

Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
50.80 +0.00/-0.38

Effective Focal Length EFL (mm):

50.80
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 50.80
Coating: Protected Silver (450-12000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥98% @ 2,000 - 12,000nm, R _{avg} (typical) 96% @ 450 - 2,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 25.4
Surface Figure, RMS: λ/2
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 450 - 12000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #47-112
Substrate: Aluminum 6061-T6
Y Offset (mm): 50.8
Reflected Wavefront, RMS: 1λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant