

TECHSPEC® 50.8 x 101.6mm EFL 90° Protected Silver 100Å Off-Axis Parabolic Mirror



Stock **#36-596** 3-4 DAYS

[Other Coating Options](#)



1



£416.50

ADD TO CART

Qty 1-5
£416.50

Qty 6+
£374.85

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
50.80 +0.00/-0.38

Effective Focal Length EFL (mm):

101.60
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 101.60
Coating: Protected Silver (450-12000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥98% @ 2,000 - 12,000nm, R _{avg} (typical) 96% @ 450 - 2,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 50.8
Surface Figure, RMS: λ/2
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 450 - 12000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #47-112
Substrate: Aluminum 6061-T6
Y Offset (mm): 101.6
Reflected Wavefront, RMS: 1λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant