

TECHSPEC® 50.8mm Dia., 9.53mm Thick, N-BK7 Uncoated Laser Window Substrate



TECHSPEC® Uncoated Laser Window Substrates

Stock **#38-059** 3-4 DAYS

⊖ 1 ⊕ **£195.50**

ADD TO CART

Qty 1-5

£195.50

Qty 6+

£175.95

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
45.72

Coating:
Uncoated

Diameter (mm):
50.80 +0.00/-0.10

Substrate: N-BK7
Index of Refraction n_d: 1.516
Surface Quality: 10-5
Thickness (mm): 9.53 ±0.20
Type: Laser Window Substrate
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 64.17
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/10
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View