

TECHSPEC®

50.8mm Dia. x 1mm Thickness, 3-12µm Coated, ZnSe Window



Stock #39-413

3-4 DAYS

-

1

+

£646.00

ADD TO CART

Qty 1-10
£646.00
Qty 11+
£581.40
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:

Protective as needed

Clear Aperture (%):

90

Clear Aperture CA (mm):

45.72

Diameter (mm): 50.80 +0.0/-0.1
Thickness (mm): 1.00 ±0.1
Coating: BBAR (3000-12000nm)
Coating Specification: R _{avg} ≤3.0% @ 3 - 12µm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.57
Density (g/cm³): 5.27
Edges: Fine Ground
Index of Refraction n_d: 2.631
Knoop Hardness (kg/mm²): 120
Parallelism (arcmin): <3
Poisson's Ratio: 0.28
Substrate: Zinc Selenide (ZnSe)
Surface Flatness (P-V): λ/10 @ 10.6µm
Surface Quality: 40-20
Type: Protective Window
Wavelength Range (nm): 3000 - 12000

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View